


28128.8 PVCF-KMP 050 15X15 YE



Wire and cable markers, Length: 50 mm, Width: 15 mm, Colour: Yellow

RAL: 1026

Business data

Article number	28128.8
Article name	PVCF-KMP 050 15X15 YE
GTIN (EAN)	4044211212698
Packaging unit	600
Quantity unit	PC
Number of markers per card	12 ST
Weight per piece (not including packaging)	0.43 g
Weight per piece (including packaging)	0.43 g
Unit of weight	G
Customs number	39204910
Country of origin	IT
Prio-Article	28128.7
Product description	Cable and wire markers

28128.8 PVCF-KMP 050 15X15 YE

Technical data

Dimensions

Length	50 mm
Length of labelling field	15 mm
Width	15 mm
Width of labelling field	15 mm

Connection data

Outer diameter of insulation, min.	6 mm
Max. outer diameter of insulation	10 mm

Materials

Marker material	PVC film
Flammability class UL 94	V-0
Working temperature, min.	-30 °C
Working temperature, max.	70 °C
Processing temperature, min.	10 °C
Processing temperature, max.	40 °C
Silicone-free	✓

Further technical data

Software code	303
---------------	-----

Environmental Product Compliance

REACH Candidate Substance Note	No
--------------------------------	----

Media

Accessories

Printer



Thermal transfer printer TTPCard including a power cord, USB cable, dust cover, black thermal transfer film (28010.4), three inlays: CCI-PC-SB 5x5 (28020.0), CCI-PC-CPM-10/BSTR (28027.0), CCI-PC/PVC/PVCF (28041.0), CONTASign PRO software in 16 languages (German, English, French, Italian, Dutch, Spanish, Portuguese, Czech, Polish, Bulgarian, Romanian, Slovenian, Turkish, Chinese, Japanese, Russian) for Windows versions 7, 8, 10. (available for download)

Article number	Article name	GTIN (EAN)	Packaging unit
<u>28000.0</u>	TTPCard Set	4044211207397	1 ST

Inlays

Printer inlay

Article number	Article name	GTIN (EAN)	Packaging unit
<u>28041.0</u>	CCI-PC/PVC/PVCF	4044211208097	1 ST