





电话 : 0769-82310511-867
邮箱 : hooya89@hooya.hk
V : hooya89


SPECIFICAIONS:
RATING: 7A 14VDC
CONTACT RESISTANCE: 50m Ω (Max)
INSULATION RESISTANCE: DC500V 1 MINUTE
OPERATING FORCE: 900 $\pm$ 300g
LIFE CYCLE: 20,000CYCLES



Circuit of Switch:



按钮黑色



5	→			DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM		
4	→			RANGE	TOLERANCE					SCALE	FIT		
3	→			X	± 0.30	ROCK TEK ELECTRICAL(SHENZHEN) CO.,LTD.				MAT'L		DRAWING NO.	REV.
2	→			X.X	± 0.20					MATERIAL NO.		WIF110021	B
1	→			X.XX	± 0.10					RT-P02-3			
NO	DESCRIPTION	APPROVED	DATE	ANGLES	$\pm 1^\circ$								