




NOTES:

- 1.Circuit:ON/OFF
- 2.Operation force:500±200gf
- 3.Electrical rating:15A 125VAC
8A 250VAC
12(6)A 250V~
- 4.Contact resistance:<50mΩ
- 5.Insulation resistance:>100MΩ(500VDC
between open contacts)
- 6.Dielectric strength:>1500V 1 minute
- 7.Color: cover is red, body is black.





Panel cut out(Thickness: 3mm Max)



Circuit of Switch



sleek is red face




电话 : 0769-82310511-867

邮箱 : hooya89@hooya.hk

V : hooya89

5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN		MM		
4	→	9	→	RANGE	TOLERANCE					SCALE		FIT		
3	→	8	→	X	±0.4					MAT'L		***		
2	→	7	→	X.X	±0.3					MATERIAL NO.		DRAWING NO.		REV
1	→	6	→	X.XX	±0.2					RT-S02-113-R42BR		WIF108023		A
NO DESCRIPTION		NO DESCRIPTION		ANGLES	±0.5°	LEGION ELECTRONIC & HARDWARE CO.,LTD								



DRAWING NO. REV

RT-S02-113-R42BR WIF108023 A