







PANEL CUTOUT THICKNESS 1.0/1.5/2.0mm

品名		面板厚度 X.X
RT-C14-010B-PP		1.0mm
RT-C14-015B-PP		1.5mm
RT-C14-020B-PP		2.0mm
RT-C14-025B-PP		2.5mm

NOTES:

- 1.Electrical rating: 10A 250VAC (VDE; CCC)
15A 250VAC (UL; CUL)
- 2.Contact resistance: 30mΩ Max
- 3.Insulation resistance: >100MΩ (Min) 500VDC
- 4.Dielectric strength: >2000VAC 0.5mA 1 minutes

电话: 0769-82310511-867
邮箱: hooya89@hooya.hk
V: hooya89

4	端子	黄铜 镀锡	3
3	本体	PA66 UL94V-0 黑色	1
2	2# PIN	黄铜 镀锡	2
1	1# PIN	黄铜 镀锡	1
NO.	PART NAME	MATERIAL	Q'TY

5		10		DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN		MM			
4		9		RANGE	TOLERANCE				LMC 2022.07.16	SCALE		NO			
3		8		X	±0.30					MAT'L		***			
2		7		X.X	±0.20					MATERIAL NO.		DRAWING NO.			REV.
1		6		X.XX	±0.10					RT-C14-020B-PP		*****			AO
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1'	ROCKTEK ELECTRICAL(SHENZHEN) CO.,LTD.									