




SINGLE SOCKET





PANEL CUTOUT DIMENSION

	THICKNESS(t)
1	0.8-0.1
2	1.3-0.1
3	1.5-0.1
4	1.8-0.1



4.8 TAB QUICKLY TERMINAL APPLICATION



NO.	部件名称	材料	用量
1	基 座	PA66 UL94V-0	1
2	1#端子	C2680 t0.4 无镀	1
3	2#端子	C2680 t0.4 无镀	1
4	3#端子	C2680 t0.4 镀镍	1
5	后 盖	PA66 UL94V-0	1

NOTES:

- 1.Rating : 15A 125VAC UL ; CUL
- 2.Contact resistance : 50mΩ Max
- 3.Insulation resistance : >100MΩ (Min) 500VDC
- 4.Dielectric strength : > 2000VAC 0.5mA 1 minutes

A 5	→	A 10	→	DIMENSIONAL TOLERANCES	APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM	LMC 2019.05.20
A 4	→	A 9	→	RANGE	TOLERANCE				SCALE	NO	
A 3	(30) → 30.3	A 8	→	X	±0.30				MAT'L	***	
A 2	更正产品刻字 2020.11.28	A 7	→	X.X	±0.20				MATERIAL NO.	DRAWING NO.	
A 1	整理图纸 2020.10.14	A 6	→	X.XX	±0.10				REV.		
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°	LEGION ELECTRONIC & HARDWARE CO., LTD.		RT-C01-A*		WIF106004	E2