











PCB. LAYOUT



SECTION A-A



NOTES:
1.Rating : 2.5A 250VAC CCC VDE
2.5A 250VAC 7A 125VAC UL CUL
2.Contact resistance : 50mΩ Max
3.Insulation resistance : >100MΩ (Min) 500VDC
4.Dielectric strength : >2000VAC 0.5mA 1 minute

品 名	颜色
RT-C08-H0-BJ	Black
RT-C08-H0-WJ	White

3	BODY	PA66 94-V0 Black	1
2	1# terminal	C2680 1/2H Tin-plating 3~5um	2
1	1# PIN	C3602 Ni-plating 3~5um	2
NO.	PART NAME	MATERIAL	Q'TY

5	4	3	2	1	10	9	8	7	6	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM	DRAWING NO.		REV.
										RANGE	TOLERANCE					SCALE	FIT			
										X	±0.3					MAT'L	***			
										X.X	±0.2					MATERIAL NO.		DRAWING NO.		REV.
										X.XX	±0.1					RT-C08-H0-*J		WIF118002		A1
NO	DESCRIPTION	NO	DESCRIPTION	NO	DESCRIPTION	NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°									

LMC
2018.01.09