



Product: [8729](#)

Electronic, 4 C #22 Str TC, PE Ins, OS, PVC Jkt, CM

Request Sample

Product Description

Electronic, 4 Conductor 22AWG (19x34) Tinned Copper, PE Insulation, Overall Beldfoil® Shield, PVC Outer Jacket, CM

Technical Specifications

Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); line level audio; voice communications; panel wiring
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	4	22 AWG	19x34	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PE - Polyethylene	0.016 in (0.41 mm)	0.062 in (1.6 mm)	Black, Red, Green, Clear

Outer Shield

Shield Type	Material	Coverage	Drainwire Type	Notes
Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (Solid) TCCS	Also has Stranded #25 drain

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.051 in (1.3 mm)	0.257 in (6.53 mm)

Overall Cable Diameter (Nominal): 0.257 in (6.53 mm)

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Conductor(s)	17.8 Ohm/1000ft	22 pF/ft (72 pF/m)	42 pF/ft (140 pF/m)	4.8 Amps per Conductor at 30°C

Voltage

UL Voltage Rating
300 V (CM), 300 V (UL AWM 2094)

Mechanical Characteristics

Temperature

UL Temperature	Operating
75°C	-20°C to +75°C

Bend Radius

Stationary Min.	Installation Min.
2.6 in (66 mm)	2.6 in (66 mm)

Max. Pull Tension: 46 lbs (21 kg)

Bulk Cable Weight:	43 lbs/1000ft
--------------------	---------------

Standards and Compliance

Environmental Suitability:	Indoor
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL 1685 UL loading , IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CM, CL3
AWM Compliance:	AWM 2094
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.478 Revision Date: 04-14-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8729 009500	White	Reel	500 ft	612825214724	C
8729 009U500	White	UnReel	500 ft	612825214700	
8729 0091000	White	Reel	1,000 ft	612825214717	C
8729 009U1000	White	UnReel	1,000 ft	612825214694	
8729 0095000	White	Reel	5,000 ft	612825214731	

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.