


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NO.	MATERIAL	MARKER SIZE inches [mm]	LABELS PER SHEET	SHEETS PER PKG.	LABELS PER PKGS.
N050X075FJJ	GMPO	0.500 [12.7] X 0.750 [19.1]	154	65	10000

CAD FILENAME/LAYERS I00472JK_C10289_N050X075FJJ_00.PRT

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
0	10-1-04	RVU		DRAWING RELEASE	0000	R		

PANDUIT CORP TINLEY PARK, ILLINOIS	
OPTIMUM N050X075FJJ LASER/INKJET PRINTABLE LABELS	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .031 (.XXX) ± .005 (.XX) ± .015 ANGLES ±	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION
DRAWN BY: RVU DATE: 10-1-04 CHK'D:	MAT'L: SEE TABLE SCALE: NTS DRAWING NO.: C10289 CNS: B SIZE: B