

Extension Cord Y Splitter, NEMA 5-15P to 2x NEMA 5-15R - 13A, 120V, 16 AWG, 18-in. (45.72 cm), Black

MODEL NUMBER: P024-18N-13A-2R



Extension cord splitter allows 2 devices with NEMA 5-15P plugs to share one AC power input cord and one NEMA 5-15R outlet.

Features

Y-Style Power Cord Splitter Connects 2 Devices with NEMA 5-15P Plugs to One AC Outlet This extension cable splitter allows two devices with NEMA 5-15P plugs to share one AC input cord and one NEMA 5-15R outlet. By connecting two devices to one outlet, the extension cord splitter frees up space in a PDU, UPS system or surge protector and helps reduce cable clutter. You can also free up valuable PDU space by connecting bulky power adapters to this splitter, preventing the adapters from blocking adjacent outlets.

Dual Cable Powers a Wide Variety of Essential Electronics With this splitter, a single NEMA 5-15R outlet can power two devices, such as computers, monitors, printers, instrument amplifiers and other equipment compatible with a 5-15P connector. Ideal for areas where AC outlets are limited, such as rack cabinets, this dual power cable is compatible with most power and extension cords.

Specifications

OVERVIEW	
UPC Code	037332180636
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	13
Voltage Compatibility (VAC)	125

Highlights

- Connects 2 devices to one AC outlet to save space and reduce cable clutter
- Recommended for powering dual computers, monitors or other compatible peripherals
- Ideal replacement for worn-out or missing extension cord Y splitter
- NEMA 5-15P plug connects to AC power; 5-15R ends connect to devices' power cords

Applications

- Connect 2 devices like computers, monitors, scanners and printers to one power outlet up to 1.5 ft. away in your home office, work space or dorm room
- Cut cable clutter by powering both monitors in a dual-monitor display mount with a single cord
- Save space in a 0U vertical rack-mount PDU by plugging two rack devices into one outlet

Package Includes

- P024-18N-13A-2R Extension Cord Y Splitter, 5-15P to 2x 5-15R, 1.5 ft., Black

PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	8.30mm
Number of Conductors	3
Wire Gauge (AWG)	16
Wire Gauge (OD - mm ²)	1.31
Cable Length (ft.)	1.5
Cable Length (m)	0.46
Shipping Dimensions (hwd / in.)	10.00 x 7.10 x 0.10
Shipping Dimensions (hwd / cm)	25.40 x 18.03 x 0.25
Shipping Weight (lbs.)	0.41
Shipping Weight (kg)	0.19
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	10% to 65% RH
Storage Humidity Range	10% to 65% RH
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	(2) NEMA 5-15R
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed

Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty