

Power Extension Cord, NEMA L5-20P to NEMA L5-20R- Heavy-Duty, 20A, 125V, 12 AWG, 15 ft. (4.57 m), Black, Locking Connectors

MODEL NUMBER: P046-015-LL



Heavy-duty extension cord connects your computer or other device with a NEMA L5-20P plug to a NEMA L5-20R outlet.

Features

Heavy-Duty Extension Cable for Network Devices That Require a Heavy-Gauge Connection This cord features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. It can be used to connect a computer, server or other device with a NEMA L5-20P plug to a wall outlet, PDU or UPS system with a NEMA L5-20R outlet. The 15-ft. (4.57 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Locking Connectors Help Prevent Accidental Disconnection and Expensive Downtime Having a cable come loose accidentally can mean the loss of power and costly downtime. Locking connectors on each end help you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

Highlights

- Recommended for powering computers, servers and other network devices
- 15-ft. (4.57 m) length allows great flexibility in placing devices in relationship to AC outlet
- Heavy-duty cord replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment
- Locking connectors maintain secure link to avoid loss of power and costly downtime

Applications

- Connect devices like computers, servers and monitors to a PDU in your data center
- Extend an existing power connection up to 15-ft. (4.57 m) to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P046-015-LL L5-20P to L5-20R Heavy-Duty Extension Cord, 15-ft. (4.57 m), Black, Locking Connectors

Specifications

| OVERVIEW | |
|-----------------------------|--|
| UPC Code | 037332190987 |
| Device Compatibility | Computer; Monitor/HDTV; Server; UPS; PDU |
| Country/Region | North America |
| INPUT | |
| Maximum Input Amps | 20 |
| Voltage Compatibility (VAC) | 125 |

| PHYSICAL | |
|--------------------------------------|-----------------------------|
| Plug Color | Black |
| Cable Jacket Color | Black |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | VW-1 |
| Power Cord Jacket Type | SJT |
| Cable Outer Diameter (OD) | 11mm |
| Number of Conductors | 3 |
| Wire Gauge (AWG) | 12 |
| Wire Gauge (OD - mm ²) | 3.31 |
| Cable Length (ft.) | 15 |
| Cable Length (m) | 4.57 |
| Cable Length (cm) | 457.20 |
| Shipping Dimensions (hwd / in.) | 14.17 x 11.80 x 0.50 |
| Shipping Dimensions (hwd / cm) | 35.99 x 29.97 x 1.27 |
| Shipping Weight (lbs.) | 2.49 |
| Shipping Weight (kg) | 1.13 |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4° to 140°F (-20° to 60°C) |
| Storage Temperature Range | -4° to 140°F (-20° to 60°C) |
| Operating Humidity Range | 10% to 65% RH |
| Storage Humidity Range | 10% to 65% RH |
| CONNECTIONS | |
| Side A - Connector 1 | NEMA L5-20P |
| Side B - Connector 1 | NEMA L5-20R |
| FEATURES & SPECIFICATIONS | |
| Antibacterial | No |
| Angled Plug | No |
| High Voltage | No |
| Locking Plug | Yes |
| Coiled Power Cord | No |
| STANDARDS & COMPLIANCE | |

| | |
|-------------------------------------|---------------------------|
| Product Certifications | cUL Listed; UL Listed |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |