

Product Features

P1CA-SAMSAM-RD316-72 is a 50 Ohm RF cable assembly, RD316 double shielded RG Type Flex coax has an outer diameter of 0.114 inch .
RD316 Double-Shielded RG Type Flex coax has an outer diameter of 0.114 inch .
k VSWR of 1.35:1



Electrical Specification: T_{Ambient} = 25° C

Parameter	Frequency Range	Units	Min	Typical	Max	Notes
Frequency Range		GHz	DC		6.0	
VSWR	DC to 0.4	1:			1.2	
	0.4 to 1.0				1.25	
	1.0 to 2.4				1.3	
	2.4 to 0.5				1.35	
Insertion Loss	DC to 0.4	dB/ft.			0.18	
	0.4 to 1.0				0.31	
	1.0 to 2.4				0.49	
	2.4 to 0.5				0.67	
Velocity Of Propagation		%		69.5		

Mechanical And Environmental Specifications:

Parameter	Description	Notes
Connector 1	SMA Male	
Connector 1 Coupling Nut	Gold Plated Brass	
Connector 1 Body	Gold Plated Brass	
Connector 1 Contact	Gold Plated Brass	
Connector 2	SMA Male	
Connector 2 Coupling Nut	Gold Plated Brass	
Connector 2 Body	Gold Plated Brass	
Connector 2 Contact	Gold Plated Brass	
Coax Cable	Double-Shielded RG Type Flex	
Cable Type	RD316	
Cable Inner Conductor	7/.0067 SPCW	
Dielectric	PTFE	
Shield	1. SPC Braid	
	2. SPC Braid	
Jacket	FEP	
Coax Diameter	0.114	
Minimum Bend Radius	0.6	
Length	72.0	
Operating Temperature	-55.0 to 125.0 °C	
RoHS Compliance	Yes	

Product Notes