

ATGBICS MTP Female-6 LC Duplex 12 Fibres OS2 9/125 Singlemode Breakout Cable, Type B, LSZH 2.0, 2m

Brand : ATGBICS

Product code:  
BOC-12MTPF-6LCOS2-2M

Product name : ATGBICS MTP Female-6 LC Duplex 12 Fibres OS2 9/125 Singlemode Breakout Cable, Type B, LSZH 2.0, 2m



ATGBICS MTP Female-6 LC Duplex 12 Fibres OS2 9/125 Singlemode Breakout Cable, Type B, LSZH 3.0, 2m

ATGBICS MTP Female-6 LC Duplex 12 Fibres OS2 9/125 Singlemode Breakout Cable, Type B, LSZH 2.0, 2m. Cable length: 2 m, Fibre optic type: OS2, Connector 1: MTP, Connector 2: 6x LC, Core diameter: 9 µm, Full duplex



Features		Features	
Cable length *	2 m	Insertion loss	0.5 dB
Connector 1 *	MTP	Return loss	50 dB
Connector 2 *	6x LC	Jacket material *	Low smoke zero halogen (LSZH)
Connector 1 gender *	Female	Polarity	B
Fibre optic type *	OS2	Country of origin	China
Product colour *	Yellow	Technical details	
Full duplex	✓	Sustainability certificates	RoHS
Core diameter	9 µm	Doesn't contain	Halogen
Cladding diameter	125 µm	Operational conditions	
Fiber mode structure	Single-mode	Operating temperature (T-T)	-10 - 70 °C
Wavelengths supported	1310,1550 nm	Storage temperature (T-T)	-40 - 85 °C
Ethernet interface type	10 Gigabit Ethernet, 40 Gigabit Ethernet	Packaging data	
		Quantity per pack	1 pc(s)



5056468744630

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 22-SEP-2023. Prints or copies of Information are only valid on the printed Publication date