

Specification Sheet

Part Number: 170-03063



A layer of aluminum provides protection from chemicals, scraping, cuts and abrasion.
Additional layer also provides insulation barrier for vulnerable wires and cables within high temperature environments.
Cuts with ordinary scissors for fast, easy application.

Braided Sleeving, Aluminum Laminated Fiberglass, 0.75" Dia, AL/GF, Silver 100 ft/reel

Article Number	170-03063
Type	BSHTTST34SR
Color	Silver (SR)
Quantity Per	reel
Product Description	High Temperature Aluminum Laminated Fiberglass Sleeving is a tubular shaped product that combines the protection of bonded aluminum and fiberglass into a single solution that is able to reflect radiant heat away from the sensitive contents inside the tube.
Short Description	Braided Sleeving, Aluminum Laminated Fiberglass, 0.75" Dia, AL/GF, Silver 100 ft/reel
Global Part Name	BSHTTST34SR-AL/GF-SR

Length L (Imperial)	100.0
---------------------	-------

Length L (Metric)	30.48
-------------------	-------

Bundle Diameter Min (Imperial)	0.1
--------------------------------	-----

Bundle Diameter Min (Metric)	2.54
------------------------------	------

Bundle Diameter Max (Imperial)	0.687
--------------------------------	-------

Bundle Diameter Max (Metric)	17.5
------------------------------	------

Diameter D (Imperial)	0.75
-----------------------	------

Diameter D (Metric)	19.1
---------------------	------

Nominal Diameter (Imperial)	0.75
-----------------------------	------

Nominal Diameter (Metric)	19.1
---------------------------	------

Wall Thickness WT (Imperial)	0.025
------------------------------	-------

Wall Thickness WT (Metric)	0.64
----------------------------	------

Material	Aluminum (AL) Glass Fiber (GF)
----------	--------------------------------

Material Shortcut	AL GF
-------------------	-------

Halogen Free	Yes
--------------	-----

UV Resistant (Yes/No)	No
Operating Temperature	-76°F to +491°F (-60°C to +255°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	30.48
Customs Number	7019905150

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).