

Specification Sheet

Part Number: MB19C2



Compact size for areas with limited mounting space.
Simple to install with a screw or rivet.
Single hole attachment with two-way entry for cable tie.

Cable Tie Anchor Mount, 0.50" x .312" .13" Hole Dia, 0.1" Max Tie Width, PA66, Natural, 100/pkg

Article Number	151-00226
Type	MB1
Color	Natural (NA)
Quantity Per	bag
Product Description	These cable tie mounts are compact in size. They are designed for simple yet robust installation particularly in areas with limited space. They pair with a cable tie for mounting applications including telecom equipment, switchgear and control cabinets.
Short Description	Cable Tie Anchor Mount, 0.50" x .312" .13" Hole Dia, 0.1" Max Tie Width, PA66, Natural, 100/pkg
Global Part Name	MB1-PA66-NA

Length L (Imperial)	0.5
Length L (Metric)	12.7
Fixation Method	Screw Mounting and Rivet
Width W (Imperial)	0.312
Width W (Metric)	7.92
Cable Ties	T18
Height H (Imperial)	.13
Height H (Metric)	3.30
Cable Tie Width Max (Imperial)	0.1
Cable Tie Width Max (Metric)	2.54
Mounting Hole Diameter D (Imperial)	0.13
Mounting Hole Diameter D (Metric)	3.3 mm
Mounting Hole Diameter D Max (Metric)	3.3
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66

Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).