

Specification Sheet

Part Number: 133-03188



Triple pipe clip secures three routings together while keeping them separated, to prevent chafing or heat transfer
Inverted retaining legs and narrow opening prevent inadvertent disengagement of pipe
Controlled flex and angled entry promote easy pipe installation

Tube and Pipe Clip, 3x4.7-5.1mm Diameter, PA66HIRHSUV, Black, 4000/ctn

Article Number	133-03188
Type	PC5X3
Color	Black (BK)
Quantity Per	carton
Product Description	This clip features a modular design that can be used individually or lined together to secure multiple pipes or hoses.
Short Description	Tube and Pipe Clip, 3x4.7-5.1mm Diameter, PA66HIRHSUV, Black, 4000/ctn
Global Part Name	PC5X3-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)	20.0
Minimum Tensile Strength (Metric)	90
Length L (Imperial)	1.03
Length L (Metric)	25.2
Width W (Imperial)	0.4
Width W (Metric)	10.16
Height H (Imperial)	0.38
Height H (Metric)	9.3
Nominal Diameter (Metric)	4.7
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	No

ROHS Compliant	Yes
Package Quantity (Imperial)	4000
Package Quantity (Metric)	4000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)