

Specification Sheet

Part Number: MP3M5.NN3P



Mounting plates allow multiple bundles to run parallel. The mounts are secured using two screws, while the bundles are attached using cable ties in any of the available slots.

Cable Tie Mounting Plate, 0.50" x 4.25", T18-T50 Cable Ties, #10 (M5) Screw, PA66, Natural, 100/pkg

|                     |                                                                                                                                                                                                                    |
|---------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 154-00500                                                                                                                                                                                                          |
| Type                | MP3M5                                                                                                                                                                                                              |
| Color               | Natural (NA)                                                                                                                                                                                                       |
| Quantity Per        | bag                                                                                                                                                                                                                |
| Product Description | HellermannTyton mounting plates allow multiple cable to be run in parallel. The mount is secured with two screws and the cables are attached to the plate by using a cable tie through any of the available slots. |
| Short Description   | Cable Tie Mounting Plate, 0.50" x 4.25", T18-T50 Cable Ties, #10 (M5) Screw, PA66, Natural, 100/pkg                                                                                                                |
| Global Part Name    | MP3M5-PA66-NA                                                                                                                                                                                                      |

|                                       |                          |
|---------------------------------------|--------------------------|
| Length L (Imperial)                   | 4.25                     |
| Length L (Metric)                     | 108.0                    |
| Fixation Method                       | Screw Mounting and Rivet |
| Width W (Imperial)                    | 0.5                      |
| Width W (Metric)                      | 12.7                     |
| Cable Ties                            | T18 - T50                |
| Height H (Imperial)                   | 0.125                    |
| Height H (Metric)                     | 3.2                      |
| Cable Tie Width Max (Imperial)        | 0.2                      |
| Cable Tie Width Max (Metric)          | 5.2                      |
| Mounting Hole Diameter D (Imperial)   | 0.2                      |
| Mounting Hole Diameter D (Metric)     | 5.1 mm                   |
| Mounting Hole Diameter D Max (Metric) | 5.1                      |
| Mounting Hole Centers (Imperial)      | 1.25                     |
| Material                              | Polyamide 6.6 (PA66)     |

|                              |                                  |
|------------------------------|----------------------------------|
| Material Shortcut            | PA66                             |
| Flammability                 | UL 94 V-2                        |
| UV Resistant (Yes/No)        | No                               |
| Operating Temperature        | -40°F to +185°F (-40°C to +85°C) |
| Reach Compliant (Article 33) | No                               |
| ROHS Compliant               | Yes                              |
| Package Quantity (Imperial)  | 100                              |
| Package Quantity (Metric)    | 100                              |
| Customs Number               | 3926909988                       |

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).