

SATA to eSATA Transition Cable (7Pin/7Pin), 2 ft.
 (0.61 m)

MODEL NUMBER: P952-002



Highlights

- Connect external eSATA drives to your SATA internal controller card
- 2ft SATA-II rated 6Gbps cable
- Plug-n-Play
- 7pin SATA "L" type connector (Internal) to 7pin "I" type connector (external)

Features

- Connect external eSATA drives to your SATA internal controller card
- SATA-II rated 6Gbps, 24", 26AWG cable
- Plug-n-Play
- 7pin SATA "L" type connector (Internal) to 7pin "I" type connector (external)

Specifications

OVERVIEW	
UPC Code	037332145932
Technology	SATA/eSATA
PHYSICAL	
Color	Red
Cable Jacket Color	Red
Cable Length (ft.)	2
Cable Length (m)	0.61
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.50
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 24.13
Shipping Weight (lbs.)	0.13
Shipping Weight (kg)	0.06

ENVIRONMENTAL	
Storage Temperature Range	-4° to 149°F (-20° to 65°C)
Operating Temperature	0 ~ 40C (32F ~ 104F)
Operating Humidity Range	10 to 90%
Storage Humidity Range	20 to 80%
CONNECTIONS	
Side A - Connector 1	7 PIN SATA (MALE)
Side B - Connector 1	7 PIN ESATA (MALE)
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty