

P1CA-24M24M-085CJ-10

2.4mm Male to 2.4mm Male RF flex cable using Flexiform 085 hand formable cable, 10 inches long, Operating to 50 GHz.

Product Features

P1dB's RF cable assembly P1CA-24M24M-085CJ-10 is a 50 Ohm hand formable cable 10 inches long with an outer diameter of 0.104 inch. It has 2.4 mm male connectors. Frequency DC to 50 GHz with a typical VSWR of 1.40 (1.45 maximum). The cable has a bend radius of 0.25 inch and a Velocity of Propagation of 70%. Typical Insertion Loss measures 1.2 dB/ft at 18 GHz and 1.8 dB/ft at 40 GHz. P1CA-24M24M-085CJ-12 is a hand formable high frequency cable assembly with good phase and amplitude stability for general purpose test applications.



Electrical Specification: T_{Ambient} = 25° C

Parameter	Frequency Range	Units	Min	Typical	Max	Notes
Frequency Range		GHz	DC		50.0	
VSWR	DC to 1.0	1:			1.2	
	1.0 to 18.0				1.25	
	18.0 to 30.0				1.35	
	30.0 to 50.0				1.45	
Insertion Loss	DC to 1.0	dB/ft.			0.2	
	1.0 to 18.0				1.3	
	18.0 to 30.0				1.5	
	30.0 to 50.0				1.95	
Velocity Of Propagation		%		70.0		

Mechanical And Environmental Specifications:

Parameter	Description	Notes
Connector 1	2.4mm Male	
Connector 1 Coupling Nut	Passivated Stainless Steel	
Connector 1 Body	Passivated Stainless Steel	
Connector 1 Contact	Gold Plated Beryllium Copper	
Connector 2	2.4mm Male	

P1CA-24M24M-085CJ-10

2.4mm Male to 2.4mm Male RF flex cable using Flexiform 085 hand formable cable, 10 inches long, Operating to 50 GHz.



Parameter	Description	Notes
Connector 2 Coupling Nut	Passivated Stainless Steel	
Connector 2 Body	Passivated Stainless Steel	
Connector 2 Contact	Gold Plated Beryllium Copper	
Coax Cable	Hand Formable	
Cable Type	Flexiform 085	
Cable Inner Conductor	SPC	
Dielectric	PTFE	
Shield	2. SPC Braid	
Jacket	FEP	
Coax Diameter	0.104	
Minimum Bend Radius	0.25	
Length	10.0	
Operating Temperature	-55.0 to 125.0 °C	
RoHS Compliance	Yes	

Product Notes