

Power Extension Cord, C19 to C20 - Heavy-Duty, 20A, 250V, 12 AWG, 2 ft. (0.61 m), Black, 6-Pack

MODEL NUMBER: P036-002-6



C19 to C20 20A heavy-duty extension cables connect high-output devices with C19/C20 power connectors, including blade server chassis.

Features

20A C20-to-C19 Power Cable for Network Devices That Require a Heavy-Gauge Connection This package of six heavy-duty extension cords features 12 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. These cords can be used to connect servers, routers, network switches and blade server enclosures to a UPS system or PDU or replace or upgrade the standard power cords provided by the devices' manufacturers. The 2-ft. (0.61 m) length helps reduce cable clutter and minimize the risk of tripping.

Specifications

OVERVIEW	
UPC Code	037332180674
Device Compatibility	Server; Router; Network Switch; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	20
Voltage Compatibility (VAC)	250
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC

Highlights

- Recommended for powering servers, routers and other high-output network devices
- 2-ft. (0.61 m) length allows flexibility in placing devices, while avoiding cable clutter
- C20 to C19 cord replaces or upgrades standard power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect devices like computers, servers and monitors to a PDU up to 2-ft. (0.61 m) away in your data center
- Extend existing power connections up to 2-ft. (0.61 m) to more easily place devices or reach a power source in a rack
- Update or replace the standard power cords provided by the original manufacturers

Package Includes

- (6) C19 to C20 Heavy-Duty Extension Cords, 2-ft. (0.61 m), Black

Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	11.2mm
Number of Conductors	3
Wire Gauge (AWG)	12
Wire Gauge (OD - mm ²)	3.31
Cable Length (ft.)	2
Cable Length (m)	0.61
Shipping Dimensions (hwd / in.)	2.25 x 9.00 x 13.00
Shipping Dimensions (hwd / cm)	5.72 x 22.86 x 33.02
Shipping Weight (lbs.)	2.80
Shipping Weight (kg)	1.27
ENVIRONMENTAL	
Operating Temperature Range	23° to 140°F (-5° to 60°C)
Storage Temperature Range	-4° to 176°F (-20° to 80°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	IEC-320-C20
Side B - Connector 1	IEC-320-C19
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.