







Bossie (博锡)

1. 温度范围(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
2. 额定电压(Rated voltage): 600V, AC, DC.
3. 额定电流(Rated current): 5.0A AC, DC.
4. 接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
5. 耐压值(Withstanding voltage): 1500V AC/minute.
6. 绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.



				
品名 (TITLE)			制图 (DR)	
MX3. 0双排弯针WTB			校对 (CHKD)	
料号 (DWG.NO)			审核 (APPD)	
BX-MX3. 0-2-5PWZ				
比例 (SCALE)	1:1	单位 (UNITS) mm		张数 (SHEET) 1 OF 1
E			F	
			A4	
			REV A	