

## 7-ft. Cat6 Gigabit Snagless Molded Ethernet Cable (RJ45 M/M) - Green

MODEL NUMBER: N201-007-GN-R



### Description

With Tripp Lite's new category 6 molded patch cables you can stay ahead of the game by using this high-speed cable to distribute data, voice and video. These cables deliver stable performance up to 550MHz. Each comes UL verified meets EIA/TIA Cat6 TIA/EIA-568-B-2.1 draft 9 standards. Constructed with high-quality copper wire and a staggered-pin plug design, near-end crosstalk levels are kept to a minimum. Designed for use in category 6, category 5e and category 5 applications. Cat6 cables are available in a variety of colors with a snagless boot preventing cable snags. Tripp Lite warrants this product to be free from defects in materials and workmanship for life. Clamshell retail packaging.

### Features

- Meets category 6 cabling standards
- Premium cabling for category 6, category 5e and category 5 applications
- Length: 7-ft. Color: green Connectors: RJ45 male
- Drastically reduce impedance & structural return loss compared to standard 100MHz wire
- High-quality copper wire and a staggered-pin plug design to keep near-end crosstalk levels to a minimum
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- PVC 4-pair stranded UTP
- Deliver stable performance up to 550MHz/1 Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 6 draft 11)
- Available in other colors and lengths
- Warranted to be free from defects in materials and workmanship for life

## Specifications

### Highlights

- Meets Category 6 cabling standards. Reduces return loss and cross talk.
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801, and ETL (Category 6, draft 11)
- Drastically reduce impedance & structural return loss compared to standard 100MHz wire.
- Snagless boots protect the locking tabs on the RJ45 connectors from being damaged during installation.
- Feature molded connectors with integral strain relief. Rated for 550 MHz/1 Gbps communication. Comes in retail packaging.
- Lifetime product warranty

### System Requirements

- For 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring TYPE 3 applications as well as EIA/TIA applications.

### Package Includes

- 7-ft. Cat6 Green Gigabit Patch Cord Snagless Molded RJ45

OVERVIEW	
UPC Code	037332116925
PHYSICAL	
Cable Jacket Color	Green
Cable Shielding	UTP
Number of Conductors	4 Pair
Cable Length (ft.)	7
Cable Length (m)	2.13
Cable Length (in.)	84
Shipping Dimensions (hwd / in.)	0.01 x 0.01 x 2.00
Shipping Dimensions (hwd / cm)	0.03 x 0.03 x 5.08
Shipping Weight (lbs.)	0.01
COMMUNICATIONS	
Attenuation @ 850NM	26.1 dB/100 m
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
Angled Connector	No
FEATURES & SPECIFICATIONS	
Antibacterial	No
IP68 Rated	No
Snagless Connector	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty