




标记 MARK	更改内容 MODIFICATION	日期 DATE	修改 DRAW	核准 APPROVE



技术要求Specification:

- 1、材质Material: PA66 UL94V-2;
- 2、塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrs, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.



线数 poles	型号 Type	尺寸Dimensions mm	
		A	B
2	ZH-2Y	1.5	3.3
3	ZH-3Y	3	4.8
4	ZH-4Y	4.5	6.3
5	ZH-5Y	6	7.8
6	ZH-6Y	7.5	9.3
7	ZH-7Y	9	10.8
8	ZH-8Y	10.5	12.3
9	ZH-9Y	12	13.8
10	ZH-10Y	13.5	15.3
11	ZH-11Y	15	16.8
12	ZH-12Y	16.5	18.3
20	ZH-20Y	28.5	30.3

TOLERANCE UNLESS OTHERWISE SPECIFIED		*: Inspection Item					
.X±0.30	X.° ±1°	(NO.)	:Cp/Cpk and SPC Control Item				
.XX±0.20	.X° ±	材料	PA66	名称	ZH1.5胶壳-10Pin		
.XXX±0.10	.XX° ±	料厚		编号	BX-ZH1.5-10PJK	单位	mm
制图		料宽		比例	1:1	版本	A
审核		日期		角法			规格书
批准		DATE					