




REV.	DESCRIPTION	APPD	DATE

弹高检测

弹高检测

端子铆压深度



PART NO:		MATERIAL:		Bossie (博锡)	
LOT NO:		FINSH:			
UNIT: MM	SIZE: A4	COLOR:			
TOLERANCES: X.X=±0.35 X.XX=±0.25 X.XXX=±0.15 GENERAL ANGLE: X.X=±3.0° X.XX=±2.0°		DR:		TITLE: 0.5mm P数:24 翻盖式 双侧触点/上下接	
		CHK: Zhou qi		DWG NO: BX-FPC05-2H24PSX	
		APP:		SCALE: 1:1	
				REV: c/o	