




- SPECIFICATIONS
- 1、Current Rating: 3A AC, DC
 - 2、Voltage Rating: 250V AC, DC
 - 3、Temperatuer Range: -25℃~+85℃
 - 4、Contact Resistance: 20mΩ Max
 - 5、Insulation Resistance: 1000MΩ Min
 - 6、Withstanding Voltang: 1000V AC/minute
 - 7、Material:Wafer Nylon66,UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
A2504-02AW	2.50	7.50
A2504-03AW	5.00	10.00
A2504-04AW	7.50	12.50
A2504-05AW	10.00	15.00
A2504-06AW	12.50	17.50
A2504-07AW	15.00	20.00
A2504-08AW	17.50	22.50
A2504-09AW	20.00	25.00
A2504-10AW	22.50	27.50
A2504-11AW	25.00	30.00
A2504-12AW	27.50	32.50
A2504-20AW	47.50	52.50

制图 DRAWN	变更内容 DESCRIPTION	日 期 DATE	GENERAL TOLERANCE		制 图 DRAWING	Zhou qi			料 号 PART NO.	BX-HA2.54-2PWZ	版 本 REV.	A				
			X.±0.25	X.°±2°	审 核 CHECK				品 名 TITLE	HA2.54 弯针 2P	页 次 SHEET	1/1				
					.X±0.20				.X°±1°	核 准 APPROVAL	客户料号 CUTM. NO.	Bossie (博锡)				
															.XX±0.15	.XX°±0.5°
				单 位 UNITS	MM	比 例 SCALE	1:1									