




| 标记<br>MARK. | 更改内容<br>MODIFICATION | 日期<br>DATE | 修改<br>DRAW | 核准<br>APPROVE |
|-------------|----------------------|------------|------------|---------------|
|             |                      |            |            |               |
|             |                      |            |            |               |
|             |                      |            |            |               |

技术要求Specification:  
1、材质Material: PA66 UL94V-0;  
2、额定电流 Current rating:2.0A AC,DC  
3、额定电压 Voltage rating: 100V AC,DC  
4、温度范围 Temperature range:-25℃to+85℃  
5、接触电阻 Contact resistance:≤20mΩ  
6、绝缘电阻 Insulation resistance:≥1000MΩ  
7、耐 压 Withstand voltage:800V AC/minute  
8、塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrs, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

| 线数 | 型 号         | 尺 寸   |       |       |
|----|-------------|-------|-------|-------|
|    |             | A     | B     | C     |
| 2  | SH20001-2Y  | 2.00  | 5.70  | 4.50  |
| 3  | SH20001-3Y  | 4.00  | 7.70  | 6.50  |
| 4  | SH20001-4Y  | 6.00  | 9.70  | 8.50  |
| 5  | SH20001-5Y  | 8.00  | 11.70 | 10.50 |
| 6  | SH20001-6Y  | 10.00 | 13.70 | 12.50 |
| 7  | SH20001-7Y  | 12.00 | 15.70 | 14.50 |
| 8  | SH20001-8Y  | 14.00 | 17.70 | 16.50 |
| 9  | SH20001-9Y  | 16.00 | 19.70 | 18.50 |
| 10 | SH20001-10Y | 18.00 | 21.70 | 20.50 |
| 11 | SH20001-11Y | 20.00 | 23.70 | 22.50 |
| 12 | SH20001-12Y | 22.00 | 25.70 | 24.50 |
| 13 | SH20001-13Y | 24.00 | 27.70 | 26.50 |
| 14 | SH20001-14Y | 26.00 | 29.70 | 28.50 |
| 15 | SH20001-15Y | 28.00 | 31.70 | 30.50 |
| 16 | SH20001-16Y | 30.00 | 33.70 | 32.50 |

|                                      |          |                    |                              |                                                                                                     |               |       |     |
|--------------------------------------|----------|--------------------|------------------------------|-----------------------------------------------------------------------------------------------------|---------------|-------|-----|
| TOLERANCE UNLESS OTHERWISE SPECIFIED |          | *: Inspection Item |                              |  Bossie ( 博锡 ) |               |       |     |
| .X±0.30                              | X. ° ±1° | NO.                | :Cp/Cpk and SPC Control Item |                                                                                                     |               |       |     |
| .XX±0.2                              | .X° ±    | 材 料                | PA66                         | 名 称                                                                                                 | PH2.0胶壳-2Pin  |       |     |
| .XXX±0.10                            | .XX° ±   | MATERIAL           |                              | 编 号                                                                                                 | BX-PH2.0-2PJK | 单 位   | m m |
| 制 图                                  |          | 料 厚                |                              | DWG NO.                                                                                             |               | 版 本   | A1  |
| 审 核                                  |          | 料 宽                |                              | 比 例                                                                                                 | 1:1           | 角 法   |     |
| CHECKED                              |          | WIDE               |                              | SCALE                                                                                               |               | PROJ. |     |
| 批 准                                  |          | 日 期                |                              | 角 法                                                                                                 |               | 规格书   |     |
| APPROVE                              |          | DATE               |                              | PROJ.                                                                                               |               |       |     |