







| 版次 | 变更摘要 | 日期 | 序号 | 品名             | 材质              |
|----|------|----|----|----------------|-----------------|
| 0  |      |    | ①  | MX3.0双排弯针WTB胶芯 | PA66 UL94V-0 黑色 |
|    |      |    | ②  | MX3.0双排弯针WTB端子 | 铜合金/表面镀锡        |



SECTION A-A

技术指标 (Technical Index):

- 温度范围 (Temperature range):  $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$ .
- 额定电压 (Rated voltage): 600V, AC, DC.
- 额定电流 (Rated current): 5.0A AC, DC.
- 接触电阻 (Contact resistance):  $\leq 20\text{m}\Omega$ .
- 耐压值 (Withstanding voltage): 1500V AC/minute.
- 绝缘电阻 (Insulation resistance):  $\geq 1000\text{M}\Omega$ .



适用线路板 (PCB LAYOUT)

| CKT  | A    | B     |
|------|------|-------|
| 2*1  |      | 6.00  |
| 2*2  | 3.0  | 9.00  |
| 2*3  | 6.0  | 12.00 |
| 2*4  | 9.0  | 15.00 |
| 2*5  | 12.0 | 18.00 |
| 2*6  | 15.0 | 21.00 |
| 2*7  | 18.0 | 24.00 |
| 2*8  | 21.0 | 27.00 |
| 2*9  | 24.0 | 30.00 |
| 2*10 | 27.0 | 33.00 |
| 2*11 | 30.0 | 36.00 |
| 2*12 | 33.0 | 39.00 |



一般公差 (TOLERANCE)  
X:  $\pm 0.50$  XX:  $\pm 1.0$   
.X:  $\pm 0.20$  .XXX:  $\pm 0.05$   
ANGLES:  $\pm 1^{\circ}$

**Bossie (博锡)**

|             |                 |            |        |
|-------------|-----------------|------------|--------|
| 品名 (TITLE)  | MX3.0双排弯针WTB    | 制图 (DR)    |        |
| 料号 (DWG.NO) | BX-MX3.0-2-8PWZ | 校对 (CHKD)  |        |
| 比例 (SCALE)  | 1:1             | 审核 (APPD)  |        |
| 单位 (UNITS)  | mm              | 张数 (SHEET) | 1 OF 1 |
|             |                 | SIZE       | A4     |
|             |                 | REV        | A      |