




标记 MARK.	更改内容 MODIFICATION	日期 DATE	修改 DRAW	核准 APPROVE

技术要求Specification:

1、材质Material: PA66 UL94V-0;

2、额定电流 Current rating:1.0A AC,DC

3、额定电压 Voltage rating: 50V AC,DC

4、温度范围 Temperature range:-25℃to+85℃

5、接触电阻 Contact resistance:≤20mΩ

6、绝缘电阻 Insulation resistance:≥100MΩ

7、耐 压 Withstand voltage:250V AC/minute

8、塑件表面平整光洁,无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrs, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

线数			尺 寸		
			A	B	C
2	SH12500-2Y	SH12501-2Y	1.25	4.30	3.00
3	SH12500-3Y	SH12501-3Y	2.50	5.55	4.25
4	SH12500-4Y	SH12501-4Y	3.75	6.80	5.50
5	SH12500-5Y	SH12501-5Y	5.00	8.05	6.75
6	SH12500-6Y	SH12501-6Y	6.25	9.30	8.00
7	SH12500-7Y	SH12501-7Y	7.50	10.55	9.25
8	SH12500-8Y	SH12501-8Y	8.75	11.80	10.50
9	SH12500-9Y	SH12501-9Y	10.00	13.05	11.75
10	SH12500-10Y	SH12501-10Y	11.25	14.30	13.00
11	SH12500-11Y	SH12501-11Y	12.50	15.55	14.25
12	SH12500-12Y	SH12501-12Y	13.75	16.80	15.50
13	SH12500-13Y	SH12501-13Y	15.00	18.05	16.75
14	SH12500-14Y	SH12501-14Y	16.25	19.30	18.00
15	SH12500-15Y	SH12501-15Y	17.50	20.55	19.25
16	SH12500-16Y	SH12501-16Y	18.75	21.80	20.50

TOLERANCE UNLESS OTHERWISE SPECIFIED		*: Inspection Item		 Bossie (博锡)			
.X±0.30	X. ° ±1°	(NO.)	:Cp/Cpk and SPC Control Item				
.XX±0.2	.X° ±	材 料	PA66	名 称	MX1.25胶壳-9Pin		
.XXX±0.10	.XX° ±	料 厚		编 号	BX-MX1.25-9PJK	单 位	m m
制 图		料 宽		DWG NO.		版 本	A
审 核		日 期		比 例	1:1	角 法	
CHECKED				角 法		规格书	
批 准				PROJ.			
APPROVE							