



Product: [83043](#)

Lead Wire, #30 Str SPC, TFE Ins, AWM 1371

Request Sample

Product Description
High Temp Plastic Lead Wire, 30AWG (7x38) Silver Plated Copper, TFE Insulation, AWM 1371 105C TYPE ET MIL-W-16878/6 250V 200C

Technical Specifications

Product Overview

Suitable Applications:	high temperature, inter-connection circuits, internal wiring of computer and electronic equipments, (Type ET) MIL-W-16878/6 applications
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
30	7x38	SC - Silvered Copper	1

Conductor Count:	1
------------------	---

Insulation

Material	Nominal Diameter	Nominal Wall Thickness
PTFE - Polytetrafluoroethylene	0.024 in	0.006 in

Electrical Characteristics

Current

Max. Recommended Current [A]
Mil-Std-975M Table 3.16 (single wire): 1.3 A

Voltage

UL Voltage Rating
250 V RMS

Temperature Range

Non-UL Temp Rating:	200°C
UL Temp Rating:	105°C

Mechanical Characteristics

Bulk Cable Weight:	0.7 lbs/1000ft
Min. Bend Radius/Minor Axis:	0.1 in

Standards

UL AWM Style Compliance:	AWM 1371
Military Compliance:	MIL-W-16878/6

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes

EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
CA Prop 65:	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	VW-1
UL voltage rating:	600 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
83043 010100	Black	Reel	100 ft	
83043 0101000	Black	Reel	1,000 ft	612825399643
83043 005100	Green, Dark	Reel	100 ft	
83043 0051000	Green, Dark	Reel	1,000 ft	
83043 002100	Red	Reel	100 ft	
83043 0021000	Red	Reel	1,000 ft	612825399636
83043 009100	White	Reel	100 ft	
83043 0091000	White	Reel	1,000 ft	

Footnote:	E - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 25'.
-----------	--

History

Update and Revision:	Revision Number: 0.360 Revision Date: 05-05-2023
----------------------	--

© 2023 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.