

Specification Sheet

Part Number: GWC003X2



Mounting hole for easy attachment using standard cable ties.

Ground Wire Tag, Cable TV Warning, Polyethylene, Orange, 25/pkg

Article Number	597-00038
----------------	-----------

Type	GW
------	----

Color	Orange (OG)
-------	-------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton ground wire tags are fabricated using .035" thick polyethylene. Vinyl is rated for outdoor use, 5-7 years. Vinyl treated with titanium dioxide ultraviolet inhibitors.
---------------------	--

Short Description	Ground Wire Tag, Cable TV Warning, Polyethylene, Orange, 25/pkg
-------------------	---

Global Part Name	GW-PE-OG
------------------	----------

Width W (Imperial)	3.0
Width W (Metric)	76.2
Height H (Imperial)	1.5
Height H (Metric)	38.1
Material	Polyethylene (PE)
Material Shortcut	PE
Adhesive	Acrylic
Halogen Free	No
UV Resistant (Yes/No)	No
Adhesive Operating Temperature	-40°F to +300°F (-40°C to +149°C)
Operating Temperature	-150°F to +149°F (-101°C to +65°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25

Customs Number	3926909988
----------------	------------

Labels per Column	1
-------------------	---

Labels per Row	1
----------------	---

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)