



SPECIFICATIONS

Current Rating: 1.5 Amps

Insulation Resistance:1000M Ω Min

Contact Resistance: 20mΩ Max

Withstanding Voltage: AC 500V

Operation Temperature:-40° to+105°

Contact Material: Brass

Standard: PA6T

Insulator Material: Polyester (UL 94V-0)

Contact Plating: Gold Flash

Max.Processing Temp: 240° C for30-60seconds
(260° C for 5 seconds)

RECOMMEND P. C. B LAYOUT

PCB TOLERANCE: ± 0.05 (TOP VIEW)

UNLESS OTHERWISE SPECIFIED TOLERANCE				DRAWN NAME: 2.0FH H6.35 2xPin 180度 Y型 PC2.8 6T								
X	: ±0.30	X°	: ±5°	SIZE	A4	SCALE	N: 1	PROUCT NO.	BX-PM2.0-2-20PY			
X.X	: ±0.25	X.X°	: ±1°	REV	A	UNIT	mm	PROJECT		PAGE	1/1	
X.XX	: ±0.20	X.XX°	: ±0.5°	CHECKED:				/ /		APPROVED:	/ /	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENAHEN YIXINYING TECHNOLOGY CO., LTD AND SHALL NOT BE REPRODUCED.COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENAHEN YIXINYING TECHNOLOGY CO., LTD												

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
1	0.00	2.00	11	20.00	22.00	21	40.00	42.00	31	60.00	62.00
2	2.00	4.00	12	22.00	24.00	22	42.00	44.00	32	62.00	64.00
3	4.00	6.00	13	24.00	26.00	23	44.00	46.00	33	64.00	66.00
4	6.00	8.00	14	26.00	28.00	24	46.00	48.00	34	66.00	68.00
5	8.00	10.00	15	28.00	30.00	25	48.00	50.00	35	68.00	70.00
6	10.00	12.00	16	30.00	32.00	26	50.00	52.00	36	70.00	72.00
7	12.00	14.00	17	32.00	34.00	27	52.00	54.00	37	72.00	74.00
8	14.00	16.00	18	34.00	36.00	28	54.00	56.00	38	74.00	76.00
9	16.00	18.00	19	36.00	38.00	29	56.00	58.00	39	76.00	78.00
10	18.00	20.00	20	38.00	40.00	30	58.00	60.00	40	78.00	80.00