







| D  | E              | F               |
|----|----------------|-----------------|
| 版次 | 变更摘要           | 日期              |
| 0  |                |                 |
| 序号 | 品名             | 材质              |
| ①  | MX3.0双排直针WTB胶芯 | PA66 UL94V-0 黑色 |
| ②  | MX3.0双排直针WTB端子 | 铜合金/表面镀锡        |



TYPE 1 (无K脚)



TYPE 2 (打K脚)




SECTION A-A

| CKT  | A    | B     |
|------|------|-------|
| 2*1  |      | 6.00  |
| 2*2  | 3.0  | 9.00  |
| 2*3  | 6.0  | 12.00 |
| 2*4  | 9.0  | 15.00 |
| 2*5  | 12.0 | 18.00 |
| 2*6  | 15.0 | 21.00 |
| 2*7  | 18.0 | 24.00 |
| 2*8  | 21.0 | 27.00 |
| 2*9  | 24.0 | 30.00 |
| 2*10 | 27.0 | 33.00 |
| 2*11 | 30.0 | 36.00 |
| 2*12 | 33.0 | 39.00 |

技术指标 (Technical Index):

- 温度范围 (Temperature range): -25° C ~ +85° C.
- 额定电压 (Rated voltage): 600V, AC, DC.
- 额定电流 (Rated current): 5.0A AC, DC.
- 接触电阻 (Contact resistance): ≤20mΩ.
- 耐压值 (Withstanding voltage): 1500V AC/minute.
- 绝缘电阻 (Insulation resistance): ≥1000MΩ.



适用线路板 (PCB LAYOUT)



一般公差 (TOLERANCE)  
X: ±.50 XX: ±1.0  
.X: ±.20 .XXX: ±.05  
ANGLES ±1°



|             |                 |            |        |
|-------------|-----------------|------------|--------|
| 品名 (TITLE)  | MX3.0双排直针WTB    | 制图 (DR)    |        |
| 料号 (DWG.NO) | BX-MX3.0-2-8PZZ | 校对 (CHKD)  |        |
| 比例 (SCALE)  | 1:1             | 审核 (APPD)  |        |
| 单位 (UNITS)  | mm              | 张数 (SHEET) | 1 OF 1 |
| 尺寸 (SIZE)   | A4              | REV        | A      |