






Pin	A	B	C
2	1.25	5.75	3.75
3	2.50	7.00	5.00
4	3.75	8.25	6.25
5	5.00	9.50	7.50
6	6.25	10.75	8.75
7	7.50	12.00	10.00
8	8.75	13.25	11.25
9	10.00	14.50	12.50
10	11.25	15.75	13.75
11	12.50	17.00	15.00
12	13.75	18.25	16.25
13	15.00	19.50	17.50
14	16.25	20.75	18.75
15	17.50	22.00	20.00
16	18.75	23.25	21.25



技术参数

间距: 1.25

温度范围: -25~+85℃


额定电压: 125V AC, DC

额定电流: 1.0A AC, DC

接触电阻: $20\text{m}\Omega$

绝缘电阻: 100M Ω

耐 压: 500V AC/minute

线性公差 / General Tolerance X. ±0.2 X.X ±0.1 X.XX ±0.05 角度公差 / Angle Tolerance X° ±5.0° X.X° ±3.0° X.XX° ±1.0°						材料 / Material			 Bossie (博锡) 品名 / ProduceName GH1.25 立贴 4P 型号 / Model BX-BX-GH1.25-4PLT
						①塑座: LCP 本色 ②接触针: 磷铜 (镀锡) ③焊片: 磷铜 (镀锡)			
	标记	变 更 内 容			签名	年月日			
	绘图	Lin L	230509				单位 (Units)	版本	
视角 / Projection 	审核	Lin R	230509				mm	2.0	1:1
	工艺			批准	Lin R	230509	共 1 张 第 1 张		