

Specification Sheet

Part Number: 111-85850



An all-in-one bundling and fixing solution reduces costs.
Disc provides secure insertion and minimizes access of dust, dirt and water.

1-Pc Cable Tie/Arrowhead Mount, 8.9"L, 50lb, Mounting Hole Dia. .27 - .28", PA66HS, Black, 100/pkg

Article Number	111-85850
Type	T50MD7
Color	Black (BK)
Quantity Per	pcs.
Product Description	The Domed Push Mount Tie provides a tight, rattle-free installation and acts as a seal to keep out dust and debris. One-piece mounting ties offer a complete solution by both bundling cable and at the same time providing a mounting solution.
Short Description	1-Pc Cable Tie/Arrowhead Mount, 8.9"L, 50lb, Mounting Hole Dia. .27 - .28", PA66HS, Black, 100/pkg
Global Part Name	T50MD7-PA66HS-BK

Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	9.0
Length L (Metric)	225.0
Fixation Method	Arrowhead
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.20
Width W (Metric)	5.0
Bundle Diameter Min (Imperial)	0.39
Bundle Diameter Min (Metric)	10.0
Bundle Diameter Max (Imperial)	2.32
Bundle Diameter Max (Metric)	59.0
Thickness T (Imperial)	0.06

Thickness T (Metric)	1.5
Panel Thickness Min (Imperial)	0.03
Panel Thickness Max (Imperial)	0.08
Panel Thickness Min (Metric)	1.2
Panel Thickness Max (Metric)	2.0
Mounting Hole Diameter D (Imperial)	0.27 - 0.28
Mounting Hole Diameter D (Metric)	6.8 - 7.2 mm
Mounting Hole Diameter D Min (Imperial)	0.27
Mounting Hole Diameter D Max (Imperial)	0.28
Mounting Hole Diameter D Max (Metric)	7.2
Disc Diameter (Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2

UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)