

## Specification Sheet

Part Number: 156-01289



The 360 degree enclosure ensures the entire bundle is secure when being routed by this clip.

Locking tab on this clip is small enough that it will not interfere with any other portion of the wire routing, but is significant enough to allow for manual disengagement if service is needed.

The cable tie portion of this two-piece design allows for two wire bundles to be routed with the same piece.

LOC Locking Clamp, 5–9 mm, Unassembled to T50R Tie, PA66HIRHSUV, Black, 1000/ctn

Article Number 156-01289

Type T50RLOC5-9-SET

Color Black (BK)

Quantity Per carton

Product Description The Locking Clip creates a full and secure lock completely around a wire bundle ranging from 10-14mm. The fixating fir tree on this clip allows for the clip to be secured into a panel by a 6mm round hole.

Short Description LOC Locking Clamp, 5–9 mm, Unassembled to T50R Tie, PA66HIRHSUV, Black, 1000/ctn

Global Part Name T50RLOC5-9-SET-PA66HS/PA66HIRHSUV-BK

|                                     |                 |
|-------------------------------------|-----------------|
| Minimum Tensile Strength (Imperial) | 50.0            |
| Minimum Tensile Strength (Metric)   | 225.0           |
| Length L (Imperial)                 | 0.93            |
| Length L (Metric)                   | 23.7            |
| Fixation Method                     | Omega Clips     |
| Identification Plate Position       | none            |
| Releasable Closure                  | No              |
| Tie Closure                         | plastic pawl    |
| Variant                             | Inside Serrated |
| Width W (Imperial)                  | 0.47            |
| Width W (Metric)                    | 12.0            |
| Bundle Diameter Min (Imperial)      | 0.20            |
| Bundle Diameter Min (Metric)        | 5.0             |
| Bundle Diameter Max (Imperial)      | 0.35            |
| Bundle Diameter Max (Metric)        | 9.0             |
| Height H (Imperial)                 | 0.93            |

|                              |                                                                                                                 |
|------------------------------|-----------------------------------------------------------------------------------------------------------------|
| Height H (Metric)            | 23.6                                                                                                            |
| Depth D (Imperial)           | 0.47                                                                                                            |
| Depth D (Metric)             | 12.0                                                                                                            |
| Material                     | Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV) Polyamide 6.6 heat stabilized (PA66HS) |
| Material Shortcut            | PA66HS PA66HIRHSUV                                                                                              |
| Flammability                 | UL 94 HB                                                                                                        |
| Halogen Free                 | Yes                                                                                                             |
| UV Resistant (Yes/No)        | Yes                                                                                                             |
| Operating Temperature        | -40°F to +230°F (-40°C to +110°C)                                                                               |
| Reach Compliant (Article 33) | Yes                                                                                                             |
| ROHS Compliant               | Yes                                                                                                             |
| Package Quantity (Imperial)  | 1000                                                                                                            |
| Package Quantity (Metric)    | 1000                                                                                                            |
| Customs Number               | 3926909988                                                                                                      |

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)