

Specification Sheet

Part Number: 117-00018



The tie contains a dual locking design to secure two bundles at once. Head design can also provide spacing between parallel bundles.

Bent tail allows for quick insertion into head.

Double-Head Cable Tie, 6.3" Long, 50lb Tensile Strength, PA66, Black, 100/pkg

Article Number	117-00018
----------------	-----------

Type	T50SDH
------	--------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	The double head cable tie was designed with a dual locking head that creates two loops to secure two bundles simultaneously. The head also provides separation between bundles or bundles running parallel to each other. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
---------------------	--

Short Description	Double-Head Cable Tie, 6.3" Long, 50lb Tensile Strength, PA66, Black, 100/pkg
-------------------	---

Global Part Name	T50SDH-PA66-BK
------------------	----------------

Minimum Tensile Strength (Imperial)	50.0
-------------------------------------	------

Minimum Tensile Strength (Metric)	225.0
-----------------------------------	-------

Length L (Imperial)	6.3
---------------------	-----

Length L (Metric)	160.0
-------------------	-------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Variant	Inside Serrated
---------	-----------------

Width W (Imperial)	0.19
--------------------	------

Width W (Metric)	4.7
------------------	-----

Bundle Diameter Min (Imperial)	0.08
--------------------------------	------

Bundle Diameter Min (Metric)	2.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.2
--------------------------------	-----

Bundle Diameter Max (Metric)	31.0
------------------------------	------

Bundle Diameter 1st Loop Max (Imperial)	1.22
---	------

Bundle Diameter 1st Loop Max (Metric)	31.0
---------------------------------------	------

Bundle Diameter 2nd Loop Max (Imperial) 1.26

Bundle Diameter 2nd Loop Max (Metric) 32.0

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL 94 V-2

Halogen Free Yes

UV Resistant (Yes/No) No

Operating Temperature -40°F to +185°F (-40°C to +85°C)

Reach Compliant (Article 33) No

ROHS Compliant Yes

UL Recognized (US) Yes

UL Recognized (US and Canada) Yes

Package Quantity (Imperial) 100

Package Quantity (Metric) 100

Customs Number 3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)