


NOTES:

- 1.MATERIAL:
  - 1.1 Housing: High Temperature Thermoplastic UL94V-0,Color:Black
  - 1.2 Terminal:Copper Alloy
  - 1.3 Stator:Copper Alloy
  - 1.4 Shell:Stainless Steel.
- 2.SPECIALITY:
  - 2.1 Rated Current:1.0A
  - 2.2 Rated Voltage:30V
  - 2.3 Contact Resistance:50mΩ Max
  - 2.4 Insulation Resistance:100MΩ Min 100V DC
  - 2.5 Dielectric Withstanding Voltage:100V AC
  - 2.6 Solder Ability:245±5°C;5±0.5s
  - 2.7 Durability:5000 cycles
  - 2.8 Operating Condition:Temperature:-30°C~+80°C; Humidity:80%R.H Max



RECOMMENDED PCB LAYOUT SPACINGS:0.705

					零件名称 TITLE		X ± 0.50 X.X ± 0.30 X.XX ± 0.20 X.XXX ± 0.08	X' ± 2 X.X' ± 1' X.XX' ± 0.5'	第三角投影法 THIRD ANGLE REFLECTION METHOD	图次 REV
					零件料号 PART NO.	PART-NO. BX-TF-1.6HJ	一般公差 GENERAL TOLERANCE		比例 比例: SCALE: 比例:	图次 图次: SHEET SHEET:
B	修改单号 ECN NO	修改描述 DESCRIPTION	确认 APPROVA BY	日期 REV	图号 DRWG NO.	DRWG-NO.	出图日期 PLOT DATE	核准 APPROVED BY	审核 CHECKED BY	设计 DESIGNER BY
A	图次 REV	变更单号 ECN NO	变更描述 DESCRIPTION	确认 APPROVA BY	日期 REV	图号 DRWG NO.	MM-DD	核准: 核准:	审核: 审核:	设计: 设计:

