




- SPECIFICATIONS
- 1、Current Rating: 3A AC, DC
 - 2、Voltage Rating: 250V AC, DC
 - 3、Temperatuer Range: -25℃~+85℃
 - 4、Contact Resistance: 20mΩ Max
 - 5、Insulation Resistance: 1000MΩ Min
 - 6、Withstanding Voltang: 1000V AC/minute
 - 7、Material:Wafer Nylon66,UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
A2504-02A	2. 50	7. 50
A2504-03A	5. 00	10. 00
A2504-04A	7. 50	12. 50
A2504-05A	10. 00	15. 00
A2504-06A	12. 50	17. 50
A2504-07A	15. 00	20. 00
A2504-08A	17. 50	22. 50
A2504-09A	20. 00	25. 00
A2504-10A	22. 50	27. 50
A2504-11A	25. 00	30. 00
A2504-12A	27. 50	32. 50
A2504-20A	47. 50	52. 50

制图 DRAWN	变更内容 DESCRIPTION	日 期 DATE	GENERL TOLERANCE		制 图 DRAWING	料 号 PART NO. 品 名 TITLE 客户料号 CUTM. NO.			版 本 REV. 页 次 SHEET	A 1/1
			X.±0.25	X.°±2°						
			.X±0.20	.X°±1°						
			.XX±0.15	.XX°±0.5°						
			.XXX±0.10	.XXX°±0.5°						
					审 核 CHECK					
					核 准 APPROVAL					
					单 位 UNITS	MM	比 例 SCALE	1:1		

B Bossie (博锡)