




QSFP56

TE Internal #: 4-2333801-4
QSFP28 Cable Assembly, 16 Positions, 6.56 ft [2 m], 56 Gb/s, Black
Cable, Shielded, 30 AWG, .051 mm², Madison TurboTwin - Round
Jacketed, QSFP28 Plug

[View on TE.com >](#)

Cable Assemblies > Copper Cable Assemblies > Pluggable I/O Cable Assemblies > QSFP56-Two QSFP56 Cable Assembly: 30 AWG



Cable Assembly Type: **QSFP28**

Equalized: **No**

Wire Size: **.051 mm²**

Outside Cable Diameter: **5.21 mm [.205 in]**

[All QSFP56-Two QSFP56 Cable Assembly: 30 AWG \(4\)](#)

Features

Product Type Features

Cable Assembly Category	High Speed, Industry Standard
Cable Assembly Type	QSFP28
Connector Type (End A)	QSFP28 Plug
Connector Type (End B)	QSFP28 Plug
Cable Style	Madison TurboTwin - Round Jacketed

Configuration Features

Number of Positions	16
Number of Pairs	8
Number of Signal Positions	16

Electrical Characteristics

Impedance	100 Ω
-----------	-------

Signal Characteristics

Data Rate	56 Gb/s
-----------	---------



Body Features

Equalized	No
Cable Color	Black
Cable Flammability Rating	CL2

Dimensions

Wire Size	.051 mm²
Outside Cable Diameter	5.21 mm[.205 in]

Operation/Application

Shielded	Yes
Halogen Free	No

Other

Cable Assembly Length	2 m[6.56 ft]
-----------------------	--------------

Product Compliance

For compliance documentation, visit the product page on TE.com>




EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 2170705-7 CAGE ASSY, QSFP28 1X1, SPRING, HS, LP	 TE Part # 2170747-6 CAGE ASSY, 1X4, QSFP28, SPRING, HS, LP	 TE Part # 2170806-5 CAGE ASSEMBLY, 1X2, QSFP28, SPRING, HS	 TE Part # 2-2170747-2 CAGE ASSY, 1X4, QSFP28, SPRING, HS, LP
 TE Part # 2170704-2 CAGE ASSY, QSFP28 1X1, SPRING, HS	 TE Part # 2227103-2 1X2 CAGE ASSY BHND BZL QSFP28	 TE Part # 2227103-1 1X2 CAGE ASSY BHND BZL QSFP28	 TE Part # 2170704-1 CAGE ASSY, QSFP28 1X1, SPRING, HS
 TE Part # 2170704-5 CAGE ASSY, QSFP28 1X1, SPRING, HS	 TE Part # 1551892-1 Cage Assy Behind Bezel QSFP28	 TE Part # 2227104-1 1X2 CAGE ASSY, BHND BEZEL, QSFP28	 TE Part # 2170703-7 CAGE ASSEMBLY, QSFP28 1X1, SPRING
 TE Part # 2170790-4 CAGE ASSY, 1X4, QSFP28, SPRING, HS, LP	 TE Part # 2170703-6 CAGE ASSEMBLY, QSFP28 1X1, SPRING	 TE Part # 1551891-1 Cage Assy, Behind Bezel, QSFP28	 TE Part # 1551920-1 zQSFP+ connector assembly
 TE Part # 2-2170808-3 QSFP28, 1X2, CAGE ASSY, SPRING, HS, LP	 TE Part # 2170704-4 CAGE ASSY, QSFP28 1X1, SPRING, HS	 TE Part # 2170806-2 CAGE ASSEMBLY, 1X2, QSFP28, SPRING, HS	 TE Part # 2170806-3 CAGE ASSEMBLY, 1X2, QSFP28, SPRING, HS

Also in the Series | QSFP56



Pluggable I/O Cable Assemblies(54)

Customers Also Bought

TE Part #4-2333842-4
QSFP56 to QSFP56 Cable Assembly:
26 AWG

TE Part #4-2334878-4
QSFP TO [4]SFP 56GIG 26AWG 2
METER

TE Part #2176049-4
RLP73M 1E R068 1% 1K RL

TE Part #1-1986711-8
SCREWLESS, SW,18P,5.0 PCB

TE Part #5-2176347-7
CRGCQ 2010 470K 1%

TE Part #4-2176363-9
RQ 0402 1K37 0.1% 10PPM 5K RL

TE Part #1-6450820-5
MBXLE VERT HDR 6P20S

TE Part #3-1879692-2
H8 21R 0.1% 100PPM

Documents

Product Drawings

QSFP TO (2)QSFP, 56G, 2 METER, 30AWG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-2333801-4_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-2333801-4_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-2333801-4_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Product Specifications

Product Specification

English

Product Specification

English