




ECN.NO.	ECN DESCRIPTION	REV.	DATE	APPD.
/	产品升级	B		
/	修改尺寸测量位置	A2		
/	依实物修改图纸	A3		



PCB.LAYOUT

备注:

1.材质:如TABLE 1;

2.主要特性:

2.1额定电流: 1.5 A

2.2接触阻抗: 30mΩ MAX\耐久后60mΩ MAX

2.3绝缘阻抗: 1000MΩ MIN

2.4耐压测试: 500V AC 一分钟

2.5额定电压: 30 V MAX;

2.6整体插入力: 35N MAX (3.57Kgf)

整体拔出力:10N min(1.02Kgf)

2.7耐久1500次

2.8产品须做焊锡测试, 粘锡面积达到95%以上;

3.0图示标有"★"符号者为重点量测尺寸;

3.1图示标有"(XX)"符号者为FAI量测尺寸;

3.2工作温度: -0°C~+50°C

3.3储存温度: -20°C~+60°C

TOLERANCE UNLESS OTHERWISE SPECIFIED	
.XXX ±0.10	.X' ±2'
.XX ±0.20	.XX' ±1'
.X ±0.30	

**IB Bossie (博锡)**

APPROVED		PART NAME:	Type-B 母座 直插			
CHECKED		PART No:	BX-TYPE-B-MZZ4P			C
DRAWN		PROJECTION:	UNIT:	SCALE:	SHEET:	REV.
DATE			mm	1:1	10F1	A2