








- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material:Wafer Nylon66, UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
A2504-02A	2.50	7.50
A2504-03A	5.00	10.00
A2504-04A	7.50	12.50
A2504-05A	10.00	15.00
A2504-06A	12.50	17.50
A2504-07A	15.00	20.00
A2504-08A	17.50	22.50
A2504-09A	20.00	25.00
A2504-10A	22.50	27.50
A2504-11A	25.00	30.00
A2504-12A	27.50	32.50
A2504-20A	47.50	52.50

 $2^{\sim}4A$ 

PCB LAYOUT

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制 图 DRAWING				料 号 PART NO.	BX-HA2.54-8PZZ	版 本 REV.	A
			X.±0.25	X.°±2°	审 核 CHECK				品 名 TITLE	HA2.54 直针 8P	页 次 SHEET	1/1
			.X±0.20	.X°±1°	核 准 APPROVAL				客户料号 CUTM. NO.			
			.XX±0.15	.XX°±0.5°					 Bossie (博锡)			
			.XXX±0.10	.XXX°±0.5°	单 位 UNITS	MM	比 例 SCALE	1:1				

