



REV.	DESCRIPTION	APPD	DATE
△/1	外壳弹片改直		
△/2	尺寸0.70改为0.55		
△/3	尺寸3.50改为2.30		
△/4	主体底部增加孔位		
△/1	增加CD PIN 高低管控		




NOTES:  
 1.MATERIAL:  
 HOUSING: HIGH TEMPERATURE THERMOPLASTIC UL94V\_0,COLOR:BLACK.  
 CONTACT: COPPER ALLOYS.  
 COVER: COPPER ALLOYS OR STEEL.  
 2.PLATING:  
 UNDERPLATE: NICKEL.  
 CONTACT AREA: GOLD OVER NICKEL.  
 SOLDER AREA: TIN OVER NICKEL.  
 3.MULTIMEDIA CARD COMPATIBLE




RECOMMENDED P.C.B HOLE LAYOUT  
 COMPONENT SIDE VIEW(TOLERANCE: +/-0.05)

PART NO: BX-TF-1.8HJ		MATERIAL:			
LOT NO:		FINSH:			
UNIT: MM	SIZE: A4	COLOR:		TITLE: MicroSD卡(TF卡) 卡座	
TOLERANCES: X.X=±0.35 X.XX=±0.25 X.XXX=±0.15		GENERAL ANGLE: X.X=±3.0° X.XX=±2.0°		DR:	DWG NO:
		CHK:		APP:	SCALE: 1:1
					SHEET: 1 OF 3
					REV: E




NO. 1

REV.	DESCRIPTION	APPD	DATE





NO. 2

1. 材质要求:
- 1.1 纸箱的材质为K-K; 外形尺寸为34\*34\*38.5;
  - 1.2 卷盘的材质为PS, 卷盘的外形尺寸为 $\phi 330 \times 30.4$ ;
  - 1.3 卷带的材质为PS, 卷带的外形尺寸为20200\*24.00\*3.0mm;
2. 包装方式:
- 2.1 将卷带放入包装机后, 前空5PCS, 后放产品1000PCS, 再后空5PCS; 上带留300MM长度。
  - 2.2 将包装好的产品从包装机上取下并包装好, 贴上内盘标签;
  - 2.3 把累叠好的12盘叠放入纸箱中共计12Kset, 上下放纸板, 纸箱四个角塞护角纸;
  - 2.4 把包装好的成品打包封箱, 并在纸箱外贴上标签



纸箱规格: 340\*340\*385

NO. 4



NO. 3

PART NO: BX-TF-1.8HJ		MATERIAL:			
LOT NO:		FINSH:			
UNIT: MM	SIZE: A4	COLOR:		TITLE:	
TOLERANCES: X.X=±0.35 X.XX=±0.25 X.XXX=±0.15		GENERAL ANGLE: X.X=±3.0° X.XX=±2.0°		DR:	
		CHK:		DWG NO:	
		APP:		SCALE: 1:1	
				SHEET: 3 OF 3	
				REV: B/3	

**Bossie (博锡)**

**Mi croSD卡(TF卡) 卡座**