








D	E	F
版次	变更摘要	日期
0		
序号	品名	材质
①	MX3.0双排直针WTB胶芯	PA66 UL94V-0 黑色
②	MX3.0双排直针WTB端子	铜合金/表面镀锡



CKT	A	B
2*1		6.00
2*2	3.0	9.00
2*3	6.0	12.00
2*4	9.0	15.00
2*5	12.0	18.00
2*6	15.0	21.00
2*7	18.0	24.00
2*8	21.0	27.00
2*9	24.0	30.00
2*10	27.0	33.00
2*11	30.0	36.00
2*12	33.0	39.00

- 技术指标 (Technical Index):
- 温度范围 (Temperature range): -25° C ~ +85° C.
 - 额定电压 (Rated voltage): 600V, AC, DC.
 - 额定电流 (Rated current): 5.0A AC, DC.
 - 接触电阻 (Contact resistance): ≤20mΩ.
 - 耐压值 (Withstanding voltage): 1500V AC/minute.
 - 绝缘电阻 (Insulation resistance): ≥1000MΩ.



一般公差 (TOLERANCE)
X: ±.50 XX: ±1.0
.X: ±.20 .XXX: ±.05
ANGLES: ±1°

品名 (TITLE)	MX3.0双排直针WTB	制图 (DR)
料号 (DWG.NO)	BX-MX3.0-2-3PZZ	校对 (CHKD)
比例 (SCALE)	1:1	审核 (APPD)
单位 (UNITS)	mm	张数 (SHEET)
		1 OF 1
		SIZE A4
		REV A