

Specification Sheet

Part Number: 151-01136

HellermannTyton Connector Clips provide a single method to mount connectors to various surfaces in a variety of applications.

Highly engineered designs feature anti-rattle discs, anti-rotation oval fir trees and clamps for mounting on edges.



An assortment of Connector Cips is available to fit the variety of connector slot designs made by most of the largest global connector manufacturers.

Conn. Clip w/Fir Tree, 0.51-6.5mm Panel Thick., 8.0x15.0 mm Hole Dia., PA66HIRHSUV, Black, 4000/ctn

Article Number	151-01136
----------------	-----------

Type	CC12
------	------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	Connector Clips feature various attachment point configurations to accommodate the many connectors on the market. They are first mated with a connector on a wire harness or cable assembly, then secured to a surface using the integrated mount. With so many configurations available, attachment surfaces can be a hole, edge, stud or even another harness assembly.
---------------------	---

Short Description	Conn. Clip w/Fir Tree, 0.51-6.5mm Panel Thick., 8.0x15.0 mm Hole Dia., PA66HIRHSUV, Black, 4000/ctn
-------------------	---

Global Part Name	CC12-PA66HIRHSUV-BK
------------------	---------------------

Length L (Imperial)	1.00
---------------------	------

Length L (Metric)	25.5
-------------------	------

Fixation Method	Fir Tree
-----------------	----------

Width W (Imperial)	0.72
--------------------	------

Width W (Metric)	18.29
------------------	-------

Height H (Imperial)	0.87
---------------------	------

Height H (Metric)	22.2
-------------------	------

Panel Thickness Min (Imperial)	0.02
--------------------------------	------

Panel Thickness Max (Imperial)	0.26
--------------------------------	------

Panel Thickness Min (Metric)	0.6
------------------------------	-----

Panel Thickness Max (Metric)	6.5
------------------------------	-----

Mounting Hole Diameter D (Imperial)	0.31 x 0.59
-------------------------------------	-------------

Mounting Hole Diameter D (Metric)	8.0 x 15.0 mm
-----------------------------------	---------------

Mounting Hole Diameter D Min (Imperial)	0.31
---	------

Mounting Hole Diameter D Max (Imperial)	0.59
---	------

Mounting Hole Diameter D Max (Metric)	15.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	4000
Package Quantity (Metric)	4000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)