






- 技术指标:
- 1. 温度范围: -25° C~85° C.
 - 2. 额定电压: 250V AC, DC.
 - 3. 耐电压: 1500V AC/minute.
 - 4. 接触电阻: ≤20mΩ .
 - 5. 绝缘电阻: ≥1000MΩ.
 - 6. 额定电流: 5A AC, DC.

CKT	A	B
2*1		5.50
2*2	4.20	9.70
2*3	8.40	13.90
2*4	12.60	18.10
2*5	16.80	22.30
2*6	21.00	26.50
2*7	25.20	30.70
2*8	29.40	34.90
2*9	33.60	39.10
2*10	37.80	43.30
2*11	42.00	47.50
2*12	46.20	51.70



一般公差 (TOLERANCE)			
X. ±.50	XX ±.10		
.X ±.20	.XXX ±.05		
ANGLES	±1°		

品名 (TITLE)		制图 (DR)	
5557双排4.2公头胶壳2代		校对 (CHKD)	
料号 (DWG.NO)		审核 (APPD)	
BX-5557-4.2-2-4P-MJK		张数 (SHEET)	
比例 (SCALE)		1 OF 1	
1:1		SIZE	
单位 (UNITS)		A4	
mm		REV	
		A	