







技术指标:

1. 温度范围:  $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$ .
2. 额定电压: 250V AC, DC.
3. 耐电压: 1500V AC/minute.
4. 接触电阻:  $\leq 20\text{m}\Omega$ .
5. 绝缘电阻:  $\geq 1000\text{M}\Omega$ .
6. 额定电流: 5A AC, DC.



| CKT  | A     | B     |
|------|-------|-------|
| 2*1  |       | 5.30  |
| 2*2  | 3.00  | 8.30  |
| 2*3  | 6.00  | 11.30 |
| 2*4  | 9.00  | 14.30 |
| 2*5  | 12.00 | 17.30 |
| 2*6  | 15.00 | 20.30 |
| 2*7  | 18.00 | 23.30 |
| 2*8  | 21.00 | 26.30 |
| 2*9  | 24.00 | 29.30 |
| 2*10 | 27.00 | 32.30 |
| 2*11 | 30.00 | 35.30 |
| 2*12 | 33.00 | 38.30 |



一般公差 (TOLERANCE)  
X:  $\pm 0.50$  XX:  $\pm 1.0$   
.X:  $\pm 0.20$  .XXX:  $\pm 0.05$   
ANGLES:  $\pm 1^{\circ}$



|             |                     |            |           |            |
|-------------|---------------------|------------|-----------|------------|
| 品名 (TITLE)  | MX3. 0-1双排母座胶壳      |            | 制图 (DR)   |            |
|             |                     |            | 校对 (CHKD) |            |
|             |                     |            | 审核 (APPD) |            |
| 料号 (DWG.NO) | BX-MX3. 0-2-11P-MJK |            |           |            |
| 比例 (SCALE)  | 1:1                 | 单位 (UNITS) | mm        | 张数 (SHEET) |
|             |                     |            |           | 1 OF 1     |
|             |                     |            |           | SIZE       |
|             |                     |            |           | A4         |
|             |                     |            |           | REV        |
|             |                     |            |           | A          |