




|    |      |
|----|------|
| E  | F    |
| 版次 | 变更摘要 |
| 0  |      |
|    | 日期   |



- 技术指标:
1. 温度范围:  $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$ .
  2. 额定电压: 250V AC, DC.
  3. 耐电压: 1500V AC/minute.
  4. 接触电阻:  $\leq 20\text{m}\Omega$ .
  5. 绝缘电阻:  $\geq 1000\text{M}\Omega$ .
  6. 额定电流: 5A AC, DC.

| CKT  | A     | B     |
|------|-------|-------|
| 2*1  |       | 5.50  |
| 2*2  | 4.20  | 9.70  |
| 2*3  | 8.40  | 13.90 |
| 2*4  | 12.60 | 18.10 |
| 2*5  | 16.80 | 22.30 |
| 2*6  | 21.00 | 26.50 |
| 2*7  | 25.20 | 30.70 |
| 2*8  | 29.40 | 34.90 |
| 2*9  | 33.60 | 39.10 |
| 2*10 | 37.80 | 43.30 |
| 2*11 | 42.00 | 47.50 |
| 2*12 | 46.20 | 51.70 |



一般公差 (TOLERANCE)  
X:  $\pm 0.50$  XX:  $\pm 1.0$   
.X:  $\pm 0.20$  .XXX:  $\pm 0.05$   
ANGLES:  $\pm 1^{\circ}$



|             |                      |            |        |
|-------------|----------------------|------------|--------|
| 品名 (TITLE)  | 5557双排4.2公头胶壳2代      | 制图 (DR)    |        |
| 料号 (DWG.NO) | BX-5557-4.2-2-9P-MJK | 校对 (CHKD)  |        |
| 比例 (SCALE)  | 1:1                  | 审核 (APPD)  |        |
| 单位 (UNITS)  | mm                   | 张数 (SHEET) | 1 OF 1 |
| 尺寸 (SIZE)   | A4                   | REV        | A      |