



SPECIFICATIONS

Current Rating:	3Amps
Insulation Resistance:	1000M Ω Min
Contact Resistance:	20m Ω Max
Withstanding Voltage:	AC 1000V
Operation Temperature:	-40° to+105°
Contact Material:	Brass
Standard:	PA6T
Insulator Material:	Polyester(UL 94V-0)
Contact Plating:	Gold Flash
Max.Processing Temp:	240° C for30-60seconds (260° C for5seconds)

RECOMMEND P. C. B LAYOUT
PCB TOLERANCE: ± 0.05 (TOP VIEW)



UNLESS OTHERWISE SPECIFIED TOLERANCE X :±0.30 X° :±5° X.X :±0.25 X.X° :±1° X.XX :±0.20 X.XX° :±0.5°		DRAW NAME: 2.54FH H8.5 2xnPin 180度 Y型 PC3.2 6T							
		SIZE	A4	SCALE	N:1	PROUCT NO.	BX-PM2.54-2-5PY		
		REV	A	UNIT	mm	PROJECT		PAGE	1/1
		CHECKED:				APPROVED:			
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN YIXINING TECHNOLOGY CO., LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENAHEN YIXINING TECHNOLOGY CO., LTD									

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
1	0.00	2.54	11	25.40	27.94	21	50.80	53.34	31	76.20	78.74
2	2.54	5.08	12	27.94	30.48	22	53.34	55.88	32	78.74	81.28
3	5.08	7.62	13	30.48	33.02	23	55.88	58.42	33	81.28	83.82
4	7.62	10.16	14	33.02	35.56	24	58.42	60.96	34	83.82	86.36
5	10.16	12.70	15	35.56	38.10	25	60.96	63.50	35	86.36	88.90
6	12.70	15.24	16	38.10	40.64	26	63.50	66.04	36	88.90	91.44
7	15.24	17.78	17	40.64	43.18	27	66.04	68.58	37	91.44	93.98
8	17.78	20.32	18	43.18	45.72	28	68.58	71.12	38	93.98	96.52
9	20.32	22.86	19	45.72	48.26	29	71.12	73.66	39	96.52	99.06
10	22.86	25.40	20	48.26	50.80	30	73.66	76.20	40	99.06	101.60