










SECTION A-A
SCALE 1:1



技术指标:

1. 温度范围: -25° C ~ 85° C.
2. 额定电压: 250V AC, DC.
3. 耐电压: 1500V AC/minute.
4. 接触电阻: ≤ 20mΩ .
5. 绝缘电阻: ≥ 1000MΩ.
6. 额定电流: 5A AC, DC.


CKT	DIM A	DIM B
1	/	5.40
2	4.20	9.60
3	8.40	13.80
4	12.60	18.00
5	16.80	22.20
6	21.00	26.40
7	25.20	30.60
8	29.40	34.80
9	33.60	39.00
10	37.80	43.20
11	42.00	47.40
12	46.20	51.60

Bossie (博锡)

品名 (TITLE)	5557双排直针WTB-2代	制图 (DR)	
料号 (DWG.NO)	BX-5557-4.2-2-1PZZ	校对 (CHKD)	
比例 (SCALE)	1:1	审核 (APPD)	
单位 (UNITS)	mm	张数 (SHEET)	1 OF 2
尺寸 (SIZE)	A4	REV	A



一般公差 (TOLERANCE)
X. ±.50 XX ±.10
.X ±.20 .XXX ±.05
ANGLES ±1°



一般公差 (TOLERANCE)
X: ± 0.50 XX: ± 1.0
.X: ± 0.20 .XXX: ± 0.05
ANGLES: $\pm 1^\circ$

Bossie (博锡)

品名 (TITLE)	5557双排直针WTB-2代	制图 (DR)		
		校对 (CHKD)		
料号 (DWG.NO)	BX-5557-4.2-2-1PZZ	审核 (APPD)		
		张数 (SHEET) 2 OF 2		
比例 (SCALE)	1:1	单位 (UNITS)	mm	REV A