

Specification Sheet

Part Number: 161-64416



Unique open design for easy branch-offs at any point along the harness. Overwrap formation provides abrasion protection and accommodates multiple bundle configurations.

Flexible construction and design eliminates pinch points and minimizes bending fatigue, making it ideal for applications involving movement and vibration.

Split shape allows for future access without disassembly.

Helawrap, HWPP25, 1" (25mm) Dia, PP, White, 100 ft/reel

|                     |                                                                                                                                                                                                                                                                                                                                                                             |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Article Number      | 161-64416                                                                                                                                                                                                                                                                                                                                                                   |
| Type                | HWPP25                                                                                                                                                                                                                                                                                                                                                                      |
| Color               | White (WH)                                                                                                                                                                                                                                                                                                                                                                  |
| Quantity Per        | reel                                                                                                                                                                                                                                                                                                                                                                        |
| Product Description | The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Helawrap easily wraps around cables with a "zipper-like" motion to protect against abrasion and mechanical stress caused by movement and bending. A handy application tool is included in every package for faster installations. |
| Short Description   | Helawrap, HWPP25, 1" (25mm) Dia, PP, White, 100 ft/reel                                                                                                                                                                                                                                                                                                                     |

Global Part Name HWPP25-PP-WH

Length L (Imperial) 100.0

Length L (Metric) 30.48

Variant Spiral Binding

Bundle Diameter Min (Imperial) 0.91

Bundle Diameter Min (Metric) 23.11

Bundle Diameter Max (Imperial) 1.06

Bundle Diameter Max (Metric) 26.92

Diameter D (Imperial) 1.0

Diameter D (Metric) 25.40

Nominal Diameter (Imperial) 1

Nominal Diameter (Metric) 25.0

Wall Thickness WT (Imperial) 0.041

Wall Thickness WT (Metric) 1.05

Material Polypropylene (PP)

|                              |                                               |
|------------------------------|-----------------------------------------------|
| Material Shortcut            | PP                                            |
| Flammability                 | UL 94 HB                                      |
| Halogen Free                 | Yes                                           |
| UV Resistant (Yes/No)        | No                                            |
| Operating Temperature        | -76°F to +230°F (-60°C to +110°C)             |
| Reach Compliant (Article 33) | Yes                                           |
| ROHS Compliant               | Yes                                           |
| Certification/Specification  | EDAG-LAB   ECE R-118-03 Abschnitt 6 / Annex 6 |
| Package Quantity (Imperial)  | 100                                           |
| Package Quantity (Metric)    | 30.48                                         |
| Customs Number               | 3926909988                                    |

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

