



| ECN.NO. | ECN DESCRIPTION | REV. | DATE | APPD. |
|---------|-----------------|------|------|-------|
| / | 更新标注 | B | | |
| / | 依实物修改图面 | C | | |
| / | 修改LAYOUT尺寸 | D | | |



备注:

电气性能:

接触阻抗: 30 毫欧 (最大)
绝缘阻抗: 100 兆欧 (最小)
耐高压: 500V AC 一分钟

电镀:

端子: 接触区域镀金
焊接区镀雾锡 100u"Min
外壳: 全区域镀镍 50u"Min
标有"★"为重点检验尺寸.

| TOLERANCE UNLESS OTHERWISE SPECIFIED | | Bossie (博锡) | |
|--------------------------------------|-------|-------------|----------------|
| .XXX | ±0.10 | PART NAME: | HDMI 母 P数: 19 |
| .XX | ±0.20 | PART No: | BX-HDMI-1-M19P |
| .X | ±0.30 | PROJECTION: | C |
| .XX | ±1" | UNIT: | 1:1 |
| | | SCALE: | 10F1 |
| | | SHEET: | D |
| APPROVED | | REV.: | |
| CHECKED | | | |
| DRAWED | | | |
| DATE | | | |

